

FM 25 – FM 170

Medical filter

- bacteria filtration rate 0.0001 %, incl. ball valve and drain flask (250 ml)
- max. operating temperature 60°C, lacquer-finished in RAL 9003 (white)

Medizin-Filter

- Bakterienfiltration 0,0001 %, inkl. Kugelhahn und Sekretauffangglas (250 ml)
- max. Betriebstemperatur 60°C, Lackierung in RAL 9003 (weiß)

Filtre à usage médical


- filtration des bactéries 0,0001 %, robinet et bac collecteur de sécrétions (250 ml) incl.
- température max. de service 60°C, peinture RAL 9003 (blanc)

Filtro per applicazioni medicali

- infiltrazione batterica 0,0001 %, con rubinetto e bicchiere di raccolta secrezione compreso (250 ml)
- pressione d'esercizio max. 60°C, verniciature in RAL 9003 (bianco)

Filtro de medicina

- filtración de bacterias del 0,0001 %, incl. grifo esférico y vidrio de recogida de secreciones (250 ml)
- temperatura de funcionamiento máx. 60 °C, lacado en RAL 9003 (blanco)



Wall mount
Wandhalterung
Fixation murale
Staffa di supporto
a parete
Soporte de pared

	for • für • pour • per • para FM 25 DPM - FM 70 DPM no. 76930307000 ³⁾	FM 90 DPM - FM 130 DPM no. 76930313000 ³⁾
n	82.5	125
o	40	75
p	35	50
q	15	16
r	8.5	15
s	20	40
t	R3.25	R4.25
u	30°	45°
v	46	82
w	8.5	13
x	50	70
y	3	4
z	31	65

3) 2 pieces • Stück • pièces • pezzi • piezas

	[m ³ /h] nominal (-677 mbar)	[m ³ /h] max. (-917 mbar)	[m ³ /h] atm.	[mm]							M	Order No. Bestell-Nr. Référence Codice d'ord N.º de pedido		Replacement cartridge Ersatzpatrone Cartouche de remplacement Sostituzione della cartuccia Cartucho de recambio
				g	a	b	c	e	f	h ¹⁾		FM ...	FM ... DPM ²⁾	
FM 25 DPM ²⁾	5.4	18	1.8	1/4"	90	80	220	21	46	110	M6	74005002500	74007002500	90951005000
FM 50 DPM ²⁾	18	60	6	3/8"	90	80	220	21	46	110	M6	74005005000	74007005000	90951005000
FM 70 DPM ²⁾	36	120	12	1/2"	90	80	281	21	46	160	M6	74005007000	74007007000	90951007000
FM 90 DPM ²⁾	45	150	15	3/4"	130	122	332	40	82	260	M8	74005009000	74007009000	90951009000
FM 110 DPM ²⁾	105	350	35	1"	130	122	478	40	82	310	M8	74005011000	74007011000	90951011000
FM 120 DPM ²⁾	210	700	70	1 1/4"	130	122	482	40	82	390	M8	74005012000	74007012000	90951013000
FM 130 DPM ²⁾	336	1120	112	1 1/2"	130	122	545	40	82	435	M8	74005013000	74007013000	90951013000
FM 140 DPM ²⁾	465	1550	155	2"	184	164	704	51	-	490	M10	74005014000	74007014000	90951014000
FM 160 DPM ²⁾	555	1850	185	2"	184	164	704	51	-	560	M10	74005016000	74007016000	90951016000
FM 170 DPM ²⁾	645	2150	215	2 1/2"	250	225	620	74	-	440	M10	74005017000	74007017000	90951017000

- | | | | | |
|--|--|--|--|---|
| 1) Space for removing filter housing (removal height) | Platz für Filtergehäuseentfernung (Ausbauhöhe) | Place pour extraction du boîtier de filtre (hauteur de dégagement) | Ingombro per rimozione custodia filtro (quota di smontaggio) | Espacio para quitar carcasa del filtro (altura de desmontaje) |
| 2) FM ... DPM: with pressure differential gauge and integrated membrane for increased protection against contamination | FM ... DPM: mit Differenzdruckanzeiger und integrierter Sperrmembran für erhöhten Kontaminationsschutz | FM ... DPM: avec affichage de pression différentielle et membrane intégrée pour meilleure protection anticontamination | FM ... DPM: con manometro differenziale e otturatore a membrana integrato per una maggiore protezione anticontaminazione | FM ... DPM: con indicador de presión diferencial y membrana de cierre integrada para gran protección de contaminación |
| • Dimensions in mm | Maßangaben in mm | Mesures en mm | Misure in mm | Dimensiones en mm |